






AW183022-01-01_28_2004

SCB-100 QUICK REFERENCE LABEL  E-SERIES DEVICES EXTENDED ANALOG (EXTENDED DIGITAL) P/N 183022B-01		PIN #	SIGNAL	33	D GND	67	AI 32 (P2.7)
FACTORY DEFAULT SETTING  * TEMP. SENSOR DISABLED * ACCESSORY POWER ON		1	AI GND	34	+5 V	68	AI 40 (D GND)
		2	AI GND	35	+5 V	69	AI 33 (P2.6)
		3	AI 0	36	AI HOLD COMP	70	AI 41 (D GND)
 * TEMP. SENSOR ENABLED ON SINGLE ENDED CH 0 * ACCESSORY POWER ON		4	AI 8	37	EXT STROBE	71	AI 34 (P2.5)
		5	AI 1	38	PFI 0/AI START TRIG	72	AI 42 (D GND)
		6	AI 9	39	PFI 1/AI REF TRIG	73	AI 35 (P2.4)
 * TEMP. SENSOR ENABLED ON DIFFERENTIAL CH 0 * ACCESSORY POWER ON		7	AI 2	40	PFI 2/AI CONV CLK	74	AI 43 (D GND)
		8	AI 10	41	PFI 3/CTR 1 SOURCE	75	AI SENSE 2 (P2.3)
		9	AI 3	42	PFI 4/CTR 1 GATE	76	AI GND (D GND)
 * 100 GENERIC TERMINALS (TEMP. SENSOR AND ACCESSORY POWER OFF)		10	AI 11	43	CTR 1 OUT	77	AI 36 (P2.2)
		11	AI 4	44	PFI 5/AO SAMP CLK	78	AI 44 (D GND)
		12	AI 12	45	PFI 6/AO START TRIG	79	AI 37 (P2.1)
		13	AI 5	46	PFI 7/AI SAMP CLK	80	AI 45 (D GND)
		14	AI 13	47	PFI 8/CTR 0 SOURCE	81	AI 38 (P2.0)
		15	AI 6	48	PFI 9/CTR 0 GATE	82	AI 46 (D GND)
		16	AI 14	49	CTR 0 OUT	83	AI 39 (P1.7)
		17	AI 7	50	FREQ OUT	84	AI 47 (D GND)
		18	AI 15	51	AI 16 (P3.7)	85	AI 48 (P1.6)
		19	AI SENSE	52	AI 24 (D GND)	86	AI 56 (D GND)
		20	AO 0	53	AI 17 (P3.6)	87	AI 49 (P1.5)
		21	AO 1	54	AI 25 (D GND)	88	AI 57 (D GND)
		22	AO EXT REF	55	AI 18 (P3.5)	89	AI 50 (P1.4)
		23	AO GND	56	AI 26 (D GND)	90	AI 58 (D GND)
		NC		57	AI 19 (P3.4)	91	AI 51 (P1.3)
		24	D GND	58	AI 27 (D GND)	92	AI 59 (D GND)
		25	P0.0	59	AI 20 (P3.3)	93	AI 52 (P1.2)
		26	P0.4	60	AI 28 (D GND)	94	AI 60 (D GND)
		27	P0.1	61	AI 21 (P3.2)	95	AI 53 (P1.1)
		28	P0.5	62	AI 29 (D GND)	96	AI 61 (D GND)
		29	P0.2	63	AI 22 (P3.1)	97	AI 54 (P1.0)
		30	P0.6	64	AI 30 (D GND)	98	AI 62 (D GND)
		31	P0.3	65	AI 23 (P3.0)	99	AI 55 (+5 V)
		32	P0.7	66	AI 31 (D GND)	100	AI 63 (D GND)

ACCEPTED

By: